

Архангельск (8182)63-90-72
Астана (7172)727-132
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89
Иваново (4932)77-34-06

Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Липецк (4742)52-20-81
Киргизия (996)312-96-26-47

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Россия (495)268-04-70

Пермь (342)205-81-47
Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Казахстан (772)734-952-31

Сургут (3462)77-98-35
Тверь (4822)63-31-35
Томск (3822)98-41-53
Тула (4872)74-02-29
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Ярославль (4852)69-52-93

<https://toupstek.nt-rt.ru/> || tuo@nt-rt.ru



23.2 to C-mount 1.0X Camera Adapter

1.0X Camera Adapter

To couple ToupCam camera to microscope and
Through microscope eyepieces tube
Adjustable (Focusable) or fixed lens inside
Different reduction lenses for different sensor size
Parfocal with different microscope objective lenses
Diffraction limited MTF performance
Aperture totally coupled with your microscope exit pupil



Specification

23.2 or 31.75 to C-mount 0.75 X Camera Adaptors for Microscope and Telescope

ToupTek microscope and telescope adapters have the following characteristic :

The possible maximum size for the image sensor is 18mmX0.75=13.5mm for the 0.75X camera adapter

Item	P/N	Picture	Model	Description	Bar Code
J03	108004		AMA100	1> Fit to 1/1.8" ~ 1" sensor 2> 0.75X magnification 3> Manually focusable 4> Parfocal with the myepiece 5> C-mount to Dia.23.2mm eye tube	
J06	108008		FMA100	1> Fit to 1/1.8" ~ 1" sensor 2> 0.75X magnification 3> Fixed focal length 4>C-mount to Dia.23.2mm eye tube	